

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224740

Luminaire Tested: **LSR2WM2B20FL408035D010 2LBD\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2WM2B20FL408035D010 2LBD\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1872.7 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224740

CATALOG NUMBER: LSR2WM2B20FL408035D010 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224740

CATALOG NUMBER: LSR2WM2B20FL408035D010 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 102 | 99  | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  |
| 3   | 105 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  |  | 94  | 91  | 89  |  | 92  |
| 4   | 101 | 95  | 90  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 90  | 87  | 85  |  | 88  |
| 5   | 98  | 91  | 86  | 82  | 96  | 90  | 85  | 82  | 88  | 84  | 81  |  | 86  | 83  | 80  |  | 85  |
| 6   | 94  | 86  | 82  | 78  | 93  | 86  | 81  | 78  | 84  | 80  | 77  |  | 83  | 79  | 77  |  | 82  |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 77  | 74  | 81  | 77  | 74  |  | 80  | 76  | 73  |  | 79  |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  |  | 71  | 68  | 65  |  | 71  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1695375 |
| 5°  | 1664485 |
| 10° | 1479636 |
| 15° | 1163691 |
| 20° | 774368  |
| 25° | 444570  |
| 30° | 224574  |
| 35° | 105637  |
| 40° | 42525   |
| 45° | 21035   |
| 50° | 11570   |
| 55° | 8104    |
| 60° | 7437    |
| 65° | 4399    |
| 70° | 5436    |
| 75° | 3592    |
| 80° | 5354    |
| 85° | 0       |



TEST NUMBER: P224740

CATALOG NUMBER: LSR2WM2B20FL408035D010 2LBD\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 392.1  | 20.9      |
| 10°-20°   | 786.1  | 42.0      |
| 20°-30°   | 489.0  | 26.1      |
| 30°-40°   | 150.4  | 8.0       |
| 40°-50°   | 33.0   | 1.8       |
| 50°-60°   | 11.7   | 0.6       |
| 60°-70°   | 5.9    | 0.3       |
| 70°-80°   | 3.5    | 0.2       |
| 80°-90°   | 1.0    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1667.2 | 89.0      |
| 0°-40°    | 1817.5 | 97.1      |
| 0°-60°    | 1862.3 | 99.4      |
| 0°-90°    | 1872.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1872.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4377 |      |
| 5°  | 4281 | 392  |
| 15° | 2902 | 786  |
| 25° | 1040 | 489  |
| 35° | 223  | 150  |
| 45° | 38   | 33   |
| 55° | 12   | 12   |
| 65° | 5    | 6    |
| 75° | 2    | 3    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P224740

CATALOG NUMBER: LSR2WM2B20FL408035D010 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4376.9 |
| 2.5°  | 4357.7 |
| 5°    | 4280.8 |
| 7.5°  | 4086.2 |
| 10°   | 3761.9 |
| 12.5° | 3372.8 |
| 15°   | 2901.9 |
| 17.5° | 2387.8 |
| 20°   | 1878.6 |
| 22.5° | 1424.5 |
| 25°   | 1040.2 |
| 27.5° | 732.7  |
| 30°   | 502.1  |
| 32.5° | 338.7  |
| 35°   | 223.4  |
| 37.5° | 134.5  |
| 40°   | 84.1   |
| 42.5° | 57.7   |
| 45°   | 38.4   |
| 47.5° | 26.4   |
| 50°   | 19.2   |
| 52.5° | 16.8   |
| 55°   | 12.0   |
| 57.5° | 9.6    |
| 60°   | 9.6    |
| 62.5° | 7.2    |
| 65°   | 4.8    |
| 67.5° | 4.8    |
| 70°   | 4.8    |
| 72.5° | 4.8    |
| 75°   | 2.4    |
| 77.5° | 2.4    |
| 80°   | 2.4    |
| 82.5° | 2.4    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)