

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223267

Luminaire Tested: **LSSQWM2B20NFL258035D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20NFL258035D010 2LBDLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1732.2 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223267

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223267

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	105	101	99		107	103	100	98		101	98	96		99	97	95		96	95	93
4	106	101	97	95		104	100	97	94		98	95	93		96	94	92		95	93	91
5	103	98	94	91		102	97	94	91		95	92	90		94	91	89		93	90	89
6	101	95	91	89		99	94	91	88		93	90	88		92	89	87		91	88	87
7	98	92	89	86		97	92	88	86		91	88	85		90	87	85		89	86	85
8	96	90	86	84		95	90	86	84		89	86	83		88	85	83		87	85	83
9	94	88	84	82		93	88	84	82		87	84	82		86	83	81		85	83	81
10	92	86	82	80		91	86	82	80		85	82	80		84	82	80		84	81	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3980561
5°	3675335
10°	2487719
15°	846372
20°	310844
25°	164801
30°	84713
35°	39531
40°	12944
45°	6519
50°	3073
55°	1148
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223267

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	804.1	46.4
10°-20°	676.0	39.0
20°-30°	185.5	10.7
30°-40°	54.1	3.1
40°-50°	10.0	0.6
50°-60°	2.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1665.6	96.2
0°-40°	1719.7	99.3
0°-60°	1732.0	100.0
0°-90°	1732.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1732.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10276	
5°	9452	804
15°	2111	676
25°	386	186
35°	84	54
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223267

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	10276.5
1°	10216.8
2°	10111.0
3°	9959.1
4°	9751.0
5°	9452.4
6°	9044.6
7°	8534.5
8°	7911.7
9°	7176.3
10°	6324.9
11°	5391.6
12°	4420.8
13°	3494.3
14°	2704.3
15°	2110.6
17.5°	1190.9
20°	754.1
22.5°	537.5
25°	385.6
27.5°	273.0
30°	189.4
32.5°	133.1
35°	83.6
37.5°	34.1
40°	25.6
42.5°	18.8
45°	11.9
47.5°	6.8
50°	5.1
52.5°	3.4
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223267

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)