

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223269

Luminaire Tested: **LSSQWM2B20NFL258035D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20NFL258035D010 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1754.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223269

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223269

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	105	101	99		107	103	100	98		101	98	96		99	97	95		96	95	93
4	106	101	97	95		104	100	97	94		98	95	93		96	94	92		95	93	91
5	103	98	94	91		102	97	94	91		95	92	90		94	91	89		93	90	89
6	101	95	91	89		99	94	91	88		93	90	88		92	89	87		91	88	87
7	98	92	89	86		97	92	88	86		91	88	85		90	87	85		89	86	85
8	96	90	86	84		95	90	86	84		89	86	83		88	85	83		87	85	83
9	94	88	84	82		93	88	84	82		87	84	82		86	83	81		85	83	81
10	92	86	82	80		91	86	82	80		85	82	80		84	82	80		84	81	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4030645
5°	3721605
10°	2519027
15°	856999
20°	314760
25°	166895
30°	85786
35°	40051
40°	13096
45°	6628
50°	3134
55°	1148
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223269

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	814.2	46.4
10°-20°	684.5	39.0
20°-30°	187.9	10.7
30°-40°	54.8	3.1
40°-50°	10.1	0.6
50°-60°	2.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1686.6	96.2
0°-40°	1741.4	99.3
0°-60°	1753.8	100.0
0°-90°	1754.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1754.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10406	
5°	9571	814
15°	2137	685
25°	390	188
35°	85	55
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223269

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10405.8
1°	10345.4
2°	10238.2
3°	10084.5
4°	9873.7
5°	9571.4
6°	9158.4
7°	8641.9
8°	8011.3
9°	7266.6
10°	6404.5
11°	5459.5
12°	4476.4
13°	3538.3
14°	2738.4
15°	2137.1
17.5°	1205.9
20°	763.6
22.5°	544.2
25°	390.5
27.5°	276.4
30°	191.8
32.5°	134.8
35°	84.7
37.5°	34.6
40°	25.9
42.5°	19.0
45°	12.1
47.5°	6.9
50°	5.2
52.5°	3.5
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223269

CATALOG NUMBER: LSSQWM2B20NFL258035D010 2LBDLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)