

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224438

Luminaire Tested: **LSRWM2B05FL408050D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B05FL408050D010 2LBDL*WH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 770.8 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224438

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224438

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | 95 | 95 | 95 |
| 2 | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98 | 101 | 98 | 96 | 98 | 96 | 94 | 95 | 94 | 92 | 91 | 91 | 91 | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 91 | 94 | 91 | 89 | 92 | 90 | 88 | 87 | 87 | 87 | 87 |
| 4 | 102 | 95 | 91 | 87 | 100 | 94 | 90 | 87 | 92 | 89 | 86 | 90 | 87 | 85 | 88 | 86 | 84 | 82 | 82 | 82 | 82 |
| 5 | 98 | 91 | 86 | 82 | 96 | 90 | 85 | 82 | 88 | 84 | 81 | 87 | 83 | 81 | 85 | 82 | 80 | 79 | 79 | 79 | 79 |
| 6 | 94 | 87 | 82 | 78 | 93 | 86 | 81 | 78 | 85 | 80 | 77 | 83 | 80 | 77 | 82 | 79 | 76 | 75 | 75 | 75 | 75 |
| 7 | 91 | 83 | 78 | 75 | 89 | 82 | 78 | 74 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 8 | 87 | 79 | 75 | 71 | 86 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | 69 | 69 | 69 |
| 9 | 84 | 76 | 71 | 68 | 83 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 73 | 70 | 67 | 66 | 66 | 66 | 66 |
| 10 | 81 | 73 | 69 | 65 | 80 | 73 | 68 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 71 | 67 | 65 | 64 | 64 | 64 | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 711167 |
| 5° | 684255 |
| 10° | 602293 |
| 15° | 473072 |
| 20° | 321644 |
| 25° | 187837 |
| 30° | 95671 |
| 35° | 45253 |
| 40° | 19771 |
| 45° | 8546 |
| 50° | 4098 |
| 55° | 2634 |
| 60° | 1549 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P224438

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDL*WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 160.7 | 20.9 |
| 10°-20° | 320.8 | 41.6 |
| 20°-30° | 205.9 | 26.7 |
| 30°-40° | 65.3 | 8.5 |
| 40°-50° | 13.9 | 1.8 |
| 50°-60° | 3.6 | 0.5 |
| 60°-70° | 0.5 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 687.4 | 89.2 |
| 0°-40° | 752.8 | 97.7 |
| 0°-60° | 770.3 | 99.9 |
| 0°-90° | 770.8 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 770.8 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1836 | |
| 5° | 1760 | 161 |
| 15° | 1180 | 321 |
| 25° | 440 | 206 |
| 35° | 96 | 65 |
| 45° | 16 | 14 |
| 55° | 4 | 4 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P224438

CATALOG NUMBER: LSRWM2B05FL408050D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1836.0 |
| 2.5° | 1818.4 |
| 5° | 1759.8 |
| 7.5° | 1664.1 |
| 10° | 1531.3 |
| 12.5° | 1369.2 |
| 15° | 1179.7 |
| 17.5° | 977.6 |
| 20° | 780.3 |
| 22.5° | 595.7 |
| 25° | 439.5 |
| 27.5° | 313.5 |
| 30° | 213.9 |
| 32.5° | 143.6 |
| 35° | 95.7 |
| 37.5° | 63.5 |
| 40° | 39.1 |
| 42.5° | 24.4 |
| 45° | 15.6 |
| 47.5° | 10.7 |
| 50° | 6.8 |
| 52.5° | 4.9 |
| 55° | 3.9 |
| 57.5° | 2.9 |
| 60° | 2.0 |
| 62.5° | 1.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)