

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224789

Luminaire Tested: **LSSQWM2B20FL409035D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409035D010 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1456.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224789

CATALOG NUMBER: LSSQWM2B20FL409035D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224789

CATALOG NUMBER: LSSQWM2B20FL409035D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99	108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93	104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87	100	94	90	86		92	88	85			90	87	85			88
5	98	91	86	82	96	90	85	82		88	84	81			86	83	80			85
6	94	86	82	78	93	86	81	78		84	80	77			83	79	77			82
7	90	83	78	74	89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71	86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68	83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65	80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1318138
5°	1294128
10°	1150387
15°	904759
20°	602067
25°	345629
30°	174614
35°	82136
40°	33069
45°	16379
50°	8979
55°	6280
60°	5810
65°	3391
70°	4190
75°	2844
80°	4238
85°	0



TEST NUMBER: P224789

CATALOG NUMBER: LSSQWM2B20FL409035D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.8	20.9
10°-20°	611.2	42.0
20°-30°	380.2	26.1
30°-40°	116.9	8.0
40°-50°	25.7	1.8
50°-60°	9.1	0.6
60°-70°	4.6	0.3
70°-80°	2.7	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1296.2	89.0
0°-40°	1413.1	97.1
0°-60°	1447.9	99.4
0°-90°	1456.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1456.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3403	
5°	3328	305
15°	2256	611
25°	809	380
35°	174	117
45°	30	26
55°	9	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224789

CATALOG NUMBER: LSSQWM2B20FL409035D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3403.0
2.5°	3388.0
5°	3328.3
7.5°	3177.0
10°	2924.8
12.5°	2622.3
15°	2256.2
17.5°	1856.5
20°	1460.6
22.5°	1107.6
25°	808.7
27.5°	569.7
30°	390.4
32.5°	263.3
35°	173.7
37.5°	104.6
40°	65.4
42.5°	44.8
45°	29.9
47.5°	20.5
50°	14.9
52.5°	13.1
55°	9.3
57.5°	7.5
60°	7.5
62.5°	5.6
65°	3.7
67.5°	3.7
70°	3.7
72.5°	3.7
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)