

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B20WFL559035D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29153)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20WFL559035D010 2LBD*LI
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1480.2 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.8
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559035D010 2LBD*LI

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559035D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93						
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87						
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80						
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75						
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69						
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65						
7	83	73	67	63	82	73	67	63	72	66	63	70	66	62	69	65	62	61						
8	79	69	63	59	78	69	63	59	68	62	59	66	62	58	66	61	58	57						
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53						
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	762219
5°	730642
10°	659875
15°	578096
20°	493244
25°	413755
30°	322749
35°	222482
40°	142895
45°	86441
50°	50739
55°	28431
60°	8134
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559035D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.9	11.7
10°-20°	400.7	27.1
20°-30°	440.4	29.7
30°-40°	298.0	20.1
40°-50°	127.7	8.6
50°-60°	39.0	2.6
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.9	68.5
0°-40°	1311.8	88.6
0°-60°	1478.6	99.9
0°-90°	1480.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1480.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1968	
5°	1879	173
15°	1442	401
25°	968	440
35°	470	298
45°	158	128
55°	42	39
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559035D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1967.8
1°	1957.3
2°	1940.7
3°	1924.2
4°	1903.1
5°	1879.1
6°	1849.0
7°	1812.9
8°	1769.4
9°	1724.3
10°	1677.7
11°	1628.0
12°	1582.9
13°	1536.3
14°	1489.7
15°	1441.6
17.5°	1316.9
20°	1196.6
22.5°	1082.4
25°	968.1
27.5°	850.9
30°	721.6
32.5°	590.8
35°	470.5
37.5°	368.3
40°	282.6
42.5°	213.5
45°	157.8
47.5°	115.8
50°	84.2
52.5°	60.1
55°	42.1
57.5°	27.1
60°	10.5
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B20WFL559035D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)