

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225407

Luminaire Tested: **LSR2B20FL408040D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B20FL408040D010 2LBDC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1940.5 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225407

CATALOG NUMBER: LSR2B20FL408040D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225407

CATALOG NUMBER: LSR2B20FL408040D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83		
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79		
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76		
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72		
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69		
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67		
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1755762
5°	1725219
10°	1539067
15°	1216504
20°	811137
25°	470598
30°	235532
35°	110792
40°	43334
45°	19337
50°	9099
55°	5132
60°	1937
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225407

CATALOG NUMBER: LSR2B20FL408040D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.7	21.0
10°-20°	821.1	42.3
20°-30°	516.5	26.6
30°-40°	157.9	8.1
40°-50°	31.0	1.6
50°-60°	7.0	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1744.3	89.9
0°-40°	1902.2	98.0
0°-60°	1940.2	100.0
0°-90°	1940.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1940.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4533	
5°	4437	407
15°	3034	821
25°	1101	517
35°	234	158
45°	35	31
55°	8	7
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225407

CATALOG NUMBER: LSR2B20FL408040D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	4532.8
2.5°	4522.7
5°	4437.0
7.5°	4235.5
10°	3913.0
12.5°	3509.8
15°	3033.6
17.5°	2504.5
20°	1967.8
22.5°	1509.2
25°	1101.1
27.5°	776.0
30°	526.6
32.5°	355.3
35°	234.3
37.5°	143.6
40°	85.7
42.5°	55.4
45°	35.3
47.5°	22.7
50°	15.1
52.5°	10.1
55°	7.6
57.5°	5.0
60°	2.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)