

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224784

Luminaire Tested: **LSR2WM2B20FL408040D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408040D010 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1831.4 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224784

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224784

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	87	82	78		93	86	81	78		84	80	77		83	80	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1658073
5°	1627857
10°	1447108
15°	1138107
20°	757303
25°	434783
30°	219609
35°	103320
40°	41564
45°	20597
50°	11329
55°	7901
60°	7282
65°	4308
70°	5323
75°	3442
80°	5130
85°	0



TEST NUMBER: P224784

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	383.4	20.9
10°-20°	768.8	42.0
20°-30°	478.3	26.1
30°-40°	147.1	8.0
40°-50°	32.3	1.8
50°-60°	11.5	0.6
60°-70°	5.8	0.3
70°-80°	3.4	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1630.5	89.0
0°-40°	1777.5	97.1
0°-60°	1821.3	99.4
0°-90°	1831.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1831.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4281	
5°	4187	383
15°	2838	769
25°	1017	478
35°	218	147
45°	38	32
55°	12	11
65°	5	6
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224784

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4280.6
2.5°	4261.8
5°	4186.6
7.5°	3996.3
10°	3679.2
12.5°	3298.6
15°	2838.1
17.5°	2335.3
20°	1837.2
22.5°	1393.2
25°	1017.3
27.5°	716.6
30°	491.0
32.5°	331.3
35°	218.5
37.5°	131.6
40°	82.2
42.5°	56.4
45°	37.6
47.5°	25.8
50°	18.8
52.5°	16.4
55°	11.7
57.5°	9.4
60°	9.4
62.5°	7.0
65°	4.7
67.5°	4.7
70°	4.7
72.5°	4.7
75°	2.3
77.5°	2.3
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)