

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224641

Luminaire Tested: **LSR2WM2B20FL408040D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408040D010 2LBDLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1812.1 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224641

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224641

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			95
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			85
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			82
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			79
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			76
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			74
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1649474
5°	1617826
10°	1437078
15°	1134097
20°	756396
25°	435381
30°	220548
35°	103368
40°	42322
45°	19118
50°	9822
55°	6280
60°	3641
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224641

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.8	21.0
10°-20°	764.2	42.2
20°-30°	478.7	26.4
30°-40°	148.1	8.2
40°-50°	30.6	1.7
50°-60°	8.5	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1623.7	89.6
0°-40°	1771.8	97.8
0°-60°	1811.0	99.9
0°-90°	1812.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1812.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4258	
5°	4161	381
15°	2828	764
25°	1019	479
35°	219	148
45°	35	31
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224641

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4258.4
2.5°	4237.5
5°	4160.8
7.5°	3965.4
10°	3653.7
12.5°	3270.0
15°	2828.1
17.5°	2318.8
20°	1835.0
22.5°	1395.4
25°	1018.7
27.5°	716.3
30°	493.1
32.5°	330.3
35°	218.6
37.5°	137.2
40°	83.7
42.5°	53.5
45°	34.9
47.5°	23.3
50°	16.3
52.5°	11.6
55°	9.3
57.5°	7.0
60°	4.7
62.5°	2.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)