

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224678

Luminaire Tested: **LSR2WM2B20FL408040D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408040D010 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1814.5 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224678

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224678

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1642696
5°	1612771
10°	1433657
15°	1127520
20°	750296
25°	430723
30°	217596
35°	102375
40°	41210
45°	20378
50°	11208
55°	7834
60°	7205
65°	4308
70°	5323
75°	3442
80°	5130
85°	0



TEST NUMBER: P224678

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.9	20.9
10°-20°	761.6	42.0
20°-30°	473.8	26.1
30°-40°	145.7	8.0
40°-50°	32.0	1.8
50°-60°	11.4	0.6
60°-70°	5.8	0.3
70°-80°	3.4	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1615.3	89.0
0°-40°	1761.0	97.1
0°-60°	1804.4	99.4
0°-90°	1814.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1814.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4241	
5°	4148	380
15°	2812	762
25°	1008	474
35°	216	146
45°	37	32
55°	12	11
65°	5	6
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224678

CATALOG NUMBER: LSR2WM2B20FL408040D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4240.9
2.5°	4222.3
5°	4147.8
7.5°	3959.2
10°	3645.0
12.5°	3267.9
15°	2811.7
17.5°	2313.6
20°	1820.2
22.5°	1380.3
25°	1007.8
27.5°	709.9
30°	486.5
32.5°	328.2
35°	216.5
37.5°	130.3
40°	81.5
42.5°	55.9
45°	37.2
47.5°	25.6
50°	18.6
52.5°	16.3
55°	11.6
57.5°	9.3
60°	9.3
62.5°	7.0
65°	4.7
67.5°	4.7
70°	4.7
72.5°	4.7
75°	2.3
77.5°	2.3
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)