

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264197

Luminaire Tested: **LD2B10D010 EU2B1010SP159024 2LBSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159024 2LBSQC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 720.9 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264197

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264197

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	97	96	96	95	94	94	93	92	92	91	90																
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	95	94	94	93	92	92	91	90	89	89	88																
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	93	92	92	91	90	90	89	88	87	87	86																
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	94	92	91	91	90	90	89	88	87	87	86	86	85	85	84																
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	89	88	87	87	86	85	85	84	84	83	83																
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	88	87	87	86	85	85	84	84	83	83	82																
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	86	85	85	84	84	83	83	82	82	81	81																
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	85	85	84	84	83	83	82	82	81	81	80																
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	84	84	83	83	82	82	81	81	80	80	79	79																
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	84	83	83	82	82	81	81	80	80	79	79	78	78																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3402124
5°	2726975
10°	1190211
15°	368824
20°	128579
25°	56777
30°	25693
35°	13371
40°	7600
45°	3628
50°	2303
55°	1290
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264197

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	418.1	58.0
10°-20°	229.0	31.8
20°-30°	52.2	7.2
30°-40°	15.0	2.1
40°-50°	4.6	0.6
50°-60°	1.4	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.3	97.0
0°-40°	714.3	99.1
0°-60°	720.3	99.9
0°-90°	720.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6896	
5°	5506	418
15°	722	229
25°	104	52
35°	22	15
45°	5	5
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264197

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6895.8
1°	6810.0
2°	6631.6
3°	6354.9
4°	5974.6
5°	5506.3
6°	4932.1
7°	4290.6
8°	3621.0
9°	2972.9
10°	2375.8
11°	1870.4
12°	1472.4
13°	1158.7
14°	915.2
15°	722.1
16°	569.7
17°	453.6
18°	364.8
19°	296.7
20°	244.9
22.5°	158.3
25°	104.3
26°	88.0
27°	74.7
28°	62.9
29°	52.5
30°	45.1
32.5°	31.1
35°	22.2
37.5°	16.3
40°	11.8
42.5°	8.1
45°	5.2
47.5°	3.7
50°	3.0
52.5°	2.2
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7



TEST NUMBER: P264197

CATALOG NUMBER: LD2B10D010 EU2B1010SP159024 2LBSQC*MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)