

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2WM2B20WFL558040D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20WFL558040D010 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1669.2 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558040D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558040D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			97
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			92
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			87
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			82
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			77
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			73
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			69
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			65
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			61
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	783020
5°	778001
10°	723279
15°	634959
20°	547367
25°	468034
30°	371457
35°	258939
40°	163829
45°	99972
50°	59115
55°	32348
60°	7050
65°	6232
70°	5210
75°	6884
80°	5130
85°	10222



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558040D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.7	11.1
10°-20°	441.0	26.4
20°-30°	497.5	29.8
30°-40°	344.2	20.6
40°-50°	146.7	8.8
50°-60°	42.4	2.5
60°-70°	6.2	0.4
70°-80°	3.9	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1124.2	67.3
0°-40°	1468.4	88.0
0°-60°	1657.5	99.3
0°-90°	1669.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1669.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2022	
5°	2001	186
15°	1583	441
25°	1095	498
35°	548	344
45°	182	147
55°	48	42
65°	7	6
75°	5	4
85°	2	2
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2WM2B20WFL558040D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2021.5
2.5°	2019.2
5°	2000.9
7.5°	1939.3
10°	1838.9
12.5°	1715.7
15°	1583.4
17.5°	1446.5
20°	1327.9
22.5°	1216.1
25°	1095.1
27.5°	967.4
30°	830.5
32.5°	682.2
35°	547.6
37.5°	424.4
40°	324.0
42.5°	244.1
45°	182.5
47.5°	132.3
50°	98.1
52.5°	70.7
55°	47.9
57.5°	20.5
60°	9.1
62.5°	6.8
65°	6.8
67.5°	4.6
70°	4.6
72.5°	4.6
75°	4.6
77.5°	2.3
80°	2.3
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)