

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223014

Luminaire Tested: **LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 647.1 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223014

CATALOG NUMBER: LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223014

CATALOG NUMBER: LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97						97													
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95						95													
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92						92													
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90						90													
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88						88													
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86						86													
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84						84													
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82						82													
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80						80													
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79						79													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1487021
5°	1372982
10°	929340
15°	316196
20°	116118
25°	61587
30°	31667
35°	14753
40°	4854
45°	2465
50°	1145
55°	405
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223014

CATALOG NUMBER: LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.4	46.4
10°-20°	252.6	39.0
20°-30°	69.3	10.7
30°-40°	20.2	3.1
40°-50°	3.7	0.6
50°-60°	0.8	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.2	96.2
0°-40°	642.4	99.3
0°-60°	647.0	100.0
0°-90°	647.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3839	
5°	3531	300
15°	788	253
25°	144	69
35°	31	20
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223014

CATALOG NUMBER: LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3839.0
1°	3816.7
2°	3777.2
3°	3720.4
4°	3642.7
5°	3531.1
6°	3378.8
7°	3188.2
8°	2955.6
9°	2680.9
10°	2362.8
11°	2014.2
12°	1651.5
13°	1305.4
14°	1010.3
15°	788.5
17.5°	444.9
20°	281.7
22.5°	200.8
25°	144.1
27.5°	102.0
30°	70.8
32.5°	49.7
35°	31.2
37.5°	12.7
40°	9.6
42.5°	7.0
45°	4.5
47.5°	2.5
50°	1.9
52.5°	1.3
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223014

CATALOG NUMBER: LD2B10D010 EU2B10NFL259024 2LBDSQLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)