

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225469

Luminaire Tested: **LSSQWM2B20FL408040D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL408040D010 2LBDLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1790.3 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225469

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225469

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	95	92	103	98	94	91	96	92	90		93	91	88		91
4	101	94	90	86	99	93	89	86	91	87	85		89	86	84		88
5	97	90	85	81	95	89	84	81	87	83	80		85	82	79		84
6	93	85	80	77	92	85	80	76	83	79	76		82	78	75		81
7	89	81	76	73	88	81	76	73	80	75	72		79	75	72		78
8	86	78	73	69	85	77	73	69	76	72	69		75	72	69		75
9	83	75	70	66	82	74	69	66	73	69	66		72	69	66		72
10	80	72	67	63	79	71	66	63	70	66	63		70	66	63		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1556782
5°	1500983
10°	1320144
15°	1034726
20°	716701
25°	441536
30°	245685
35°	131077
40°	64975
45°	33141
50°	18199
55°	11886
60°	5888
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225469

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.1	19.7
10°-20°	704.8	39.4
20°-30°	481.5	26.9
30°-40°	183.5	10.3
40°-50°	51.0	2.8
50°-60°	15.9	0.9
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1538.3	85.9
0°-40°	1721.9	96.2
0°-60°	1788.8	99.9
0°-90°	1790.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1790.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4019	
5°	3860	352
15°	2580	705
25°	1033	481
35°	277	184
45°	60	51
55°	18	16
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225469

CATALOG NUMBER: LSSQWM2B20FL408040D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	4019.1
2.5°	3976.2
5°	3860.3
7.5°	3643.6
10°	3356.4
12.5°	2991.0
15°	2580.3
17.5°	2159.5
20°	1738.7
22.5°	1365.7
25°	1033.1
27.5°	758.5
30°	549.3
32.5°	390.6
35°	277.2
37.5°	194.0
40°	128.5
42.5°	85.7
45°	60.5
47.5°	42.8
50°	30.2
52.5°	22.7
55°	17.6
57.5°	12.6
60°	7.6
62.5°	2.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)