

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223922

Luminaire Tested: **LD2B10D010 EU2B10SP159024 2LBDL\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223922  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10SP159024 2LBDL\*LI  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
SPOT OPTIC  
LENSED SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 389.6 lumens  
Efficiency: N/A  
Efficacy: 37.8 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223922

CATALOG NUMBER: LD2B10D010 EU2B10SP159024 2LBDL\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P223922

CATALOG NUMBER: LD2B10D010 EU2B10SP159024 2LBDL\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98			98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96			96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94			94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93			93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91			91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90			90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88			88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87			87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86			86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85			85

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1872121
5°	1353346
10°	393990
15°	138228
20°	59193
25°	26626
30°	10287
35°	5107
40°	3438
45°	2246
50°	1205
55°	945
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223922

CATALOG NUMBER: LD2B10D010 EU2B10SP159024 2LBDL\*LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	246.3	63.2
10°-20°	100.2	25.7
20°-30°	30.8	7.9
30°-40°	7.6	1.9
40°-50°	3.2	0.8
50°-60°	1.4	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	377.3	96.8
0°-40°	384.8	98.8
0°-60°	389.4	99.9
0°-90°	389.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	389.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4833	
5°	3481	246
15°	345	100
25°	62	31
35°	11	8
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223922

CATALOG NUMBER: LD2B10D010 EU2B10SP159024 2LBDL\*LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4833.2
1°	4759.3
2°	4579.2
3°	4292.0
4°	3916.8
5°	3480.6
6°	2988.9
7°	2455.2
8°	1914.0
9°	1408.1
10°	1001.7
11°	717.9
12°	539.8
13°	439.6
14°	384.7
15°	344.7
17.5°	212.7
20°	143.6
22.5°	96.2
25°	62.3
27.5°	37.9
30°	23.0
32.5°	14.9
35°	10.8
37.5°	8.8
40°	6.8
42.5°	5.4
45°	4.1
47.5°	2.7
50°	2.0
52.5°	2.0
55°	1.4
57.5°	1.4
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223922

CATALOG NUMBER: LD2B10D010 EU2B10SP159024 2LBDL\*LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)