

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B10WFL559024 2LBDL\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10WFL559024 2LBDL\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
WIDE FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 645.8 lumens  
Efficiency: N/A  
Efficacy: 62.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559024 2LBDL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559024 2LBDL\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80			
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	302943
5°	300990
10°	279848
15°	245659
20°	211750
25°	181085
30°	143707
35°	100199
40°	63357
45°	38674
50°	22899
55°	12493
60°	2711
65°	2383
70°	2039
75°	2694
80°	2008
85°	4000



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559024 2LBDL\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.8	11.1
10°-20°	170.6	26.4
20°-30°	192.5	29.8
30°-40°	133.2	20.6
40°-50°	56.8	8.8
50°-60°	16.4	2.5
60°-70°	2.4	0.4
70°-80°	1.5	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.9	67.3
0°-40°	568.1	88.0
0°-60°	641.3	99.3
0°-90°	645.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	782	
5°	774	72
15°	613	171
25°	424	192
35°	212	133
45°	71	57
55°	18	16
65°	3	2
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559024 2LBDL\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	782.1
2.5°	781.2
5°	774.1
7.5°	750.3
10°	711.5
12.5°	663.8
15°	612.6
17.5°	559.6
20°	513.7
22.5°	470.5
25°	423.7
27.5°	374.3
30°	321.3
32.5°	263.9
35°	211.9
37.5°	164.2
40°	125.3
42.5°	94.5
45°	70.6
47.5°	51.2
50°	38.0
52.5°	27.4
55°	18.5
57.5°	7.9
60°	3.5
62.5°	2.6
65°	2.6
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)