

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225320

Luminaire Tested: **LSR2B20FL409040D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225320
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B20FL409040D010 2LBDC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1596.5 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225320

CATALOG NUMBER: LSR2B20FL409040D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225320

CATALOG NUMBER: LSR2B20FL409040D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99	108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93	104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87	100	94	90	86		92	88	85			90	87	85			88
5	98	91	86	82	96	90	85	82		88	84	81			86	83	80			85
6	94	87	82	78	93	86	81	78		84	80	77			83	80	77			82
7	90	83	78	74	89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71	86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68	83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65	80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1445343
5°	1418980
10°	1261421
15°	992059
20°	660146
25°	379009
30°	191431
35°	90080
40°	36255
45°	17968
50°	9883
55°	6888
60°	6352
65°	3758
70°	4643
75°	2993
80°	4461
85°	0



TEST NUMBER: P225320

CATALOG NUMBER: LSR2B20FL409040D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.2	20.9
10°-20°	670.1	42.0
20°-30°	416.9	26.1
30°-40°	128.2	8.0
40°-50°	28.2	1.8
50°-60°	10.0	0.6
60°-70°	5.0	0.3
70°-80°	2.9	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1421.3	89.0
0°-40°	1549.5	97.1
0°-60°	1587.7	99.4
0°-90°	1596.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1596.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3731	
5°	3649	334
15°	2474	670
25°	887	417
35°	190	128
45°	33	28
55°	10	10
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P225320

CATALOG NUMBER: LSR2B20FL409040D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3731.4
2.5°	3715.0
5°	3649.4
7.5°	3483.6
10°	3207.1
12.5°	2875.3
15°	2473.9
17.5°	2035.7
20°	1601.5
22.5°	1214.4
25°	886.8
27.5°	624.6
30°	428.0
32.5°	288.8
35°	190.5
37.5°	114.7
40°	71.7
42.5°	49.2
45°	32.8
47.5°	22.5
50°	16.4
52.5°	14.3
55°	10.2
57.5°	8.2
60°	8.2
62.5°	6.1
65°	4.1
67.5°	4.1
70°	4.1
72.5°	4.1
75°	2.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)