

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224940

Luminaire Tested: **LD2B10D010 EU2B10FL408027 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL408027 2LBD*H
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1002.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224940

CATALOG NUMBER: LD2B10D010 EU2B10FL408027 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224940

CATALOG NUMBER: LD2B10D010 EU2B10FL408027 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91			
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83			
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79			
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73			
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70			
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67			
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	929398
5°	909930
10°	801392
15°	628744
20°	417522
25°	239680
30°	120226
35°	55514
40°	22552
45°	10079
50°	5243
55°	3309
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224940

CATALOG NUMBER: LD2B10D010 EU2B10FL408027 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.7	21.3
10°-20°	424.4	42.4
20°-30°	263.7	26.3
30°-40°	79.5	7.9
40°-50°	16.2	1.6
50°-60°	4.2	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.8	90.0
0°-40°	981.3	97.9
0°-60°	1001.7	100.0
0°-90°	1002.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1002.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2399	
5°	2340	214
15°	1568	424
25°	561	264
35°	117	80
45°	18	16
55°	5	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224940

CATALOG NUMBER: LD2B10D010 EU2B10FL408027 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2399.4
1°	2391.6
2°	2381.0
3°	2373.2
4°	2361.6
5°	2340.2
6°	2306.2
7°	2259.7
8°	2192.7
9°	2117.1
10°	2037.5
11°	1953.1
12°	1864.8
13°	1772.6
14°	1671.7
15°	1567.9
17.5°	1289.4
20°	1012.9
22.5°	768.4
25°	560.8
27.5°	395.9
30°	268.8
32.5°	176.6
35°	117.4
37.5°	72.8
40°	44.6
42.5°	29.1
45°	18.4
47.5°	11.6
50°	8.7
52.5°	5.8
55°	4.9
57.5°	2.9
60°	1.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224940

CATALOG NUMBER: LD2B10D010 EU2B10FL408027 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)