

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224785

Luminaire Tested: **LSR2WM2B20FL408050D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2WM2B20FL408050D010 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1819.4 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224785

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224785

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1647111
5°	1617126
10°	1437550
15°	1130568
20°	752315
25°	431919
30°	218178
35°	102658
40°	41311
45°	20433
50°	11269
55°	7901
60°	7205
65°	4308
70°	5323
75°	3442
80°	5130
85°	0



TEST NUMBER: P224785

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.9	20.9
10°-20°	763.7	42.0
20°-30°	475.1	26.1
30°-40°	146.1	8.0
40°-50°	32.1	1.8
50°-60°	11.4	0.6
60°-70°	5.8	0.3
70°-80°	3.4	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1619.7	89.0
0°-40°	1765.8	97.1
0°-60°	1809.3	99.4
0°-90°	1819.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1819.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4252	
5°	4159	381
15°	2819	764
25°	1011	475
35°	217	146
45°	37	32
55°	12	11
65°	5	6
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224785

CATALOG NUMBER: LSR2WM2B20FL408050D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4252.3
2.5°	4233.7
5°	4159.0
7.5°	3969.9
10°	3654.9
12.5°	3276.8
15°	2819.3
17.5°	2319.9
20°	1825.1
22.5°	1384.0
25°	1010.6
27.5°	711.8
30°	487.8
32.5°	329.1
35°	217.1
37.5°	130.7
40°	81.7
42.5°	56.0
45°	37.3
47.5°	25.7
50°	18.7
52.5°	16.3
55°	11.7
57.5°	9.3
60°	9.3
62.5°	7.0
65°	4.7
67.5°	4.7
70°	4.7
72.5°	4.7
75°	2.3
77.5°	2.3
80°	2.3
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)