

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224161

Luminaire Tested: **LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 503.0 lumens
Efficiency: N/A
Efficacy: 48.8 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224161

CATALOG NUMBER: LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224161

CATALOG NUMBER: LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																												
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																												
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94																												
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																												
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91																												
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90																												
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88																												
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87																												
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86																												
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2417000
5°	1747266
10°	508683
15°	178490
20°	76423
25°	34362
30°	13284
35°	6620
40°	4399
45°	2849
50°	1567
55°	1148
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224161

CATALOG NUMBER: LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.0	63.2
10°-20°	129.4	25.7
20°-30°	39.7	7.9
30°-40°	9.8	1.9
40°-50°	4.1	0.8
50°-60°	1.7	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	487.1	96.8
0°-40°	496.9	98.8
0°-60°	502.6	99.9
0°-90°	503.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	503.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6240	
5°	4494	318
15°	445	129
25°	80	40
35°	14	10
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224161

CATALOG NUMBER: LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6239.9
1°	6144.6
2°	5912.0
3°	5541.3
4°	5056.8
5°	4493.7
6°	3858.9
7°	3169.8
8°	2471.1
9°	1817.9
10°	1293.3
11°	926.9
12°	696.9
13°	567.5
14°	496.7
15°	445.1
17.5°	274.6
20°	185.4
22.5°	124.2
25°	80.4
27.5°	49.0
30°	29.7
32.5°	19.2
35°	14.0
37.5°	11.4
40°	8.7
42.5°	7.0
45°	5.2
47.5°	3.5
50°	2.6
52.5°	2.6
55°	1.7
57.5°	1.7
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224161

CATALOG NUMBER: LD2B10D010 EU2B10SP158027 2LBDSQLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)