

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224588

Luminaire Tested: **LSSQWM2B20FL408050D010 2LBDL\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B20FL408050D010 2LBDL\*GPH  
Description: 2000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1843.6 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224588

CATALOG NUMBER: LSSQWM2B20FL408050D010 2LBDL\*GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P224588

CATALOG NUMBER: LSSQWM2B20FL408050D010 2LBDL\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 0   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 100 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  |  | 102 | 101 | 100 |  |  | 95  |
| 2   | 110 | 106 | 102 | 100 |  | 108 | 104 | 101 | 98  |  | 101 | 99  | 96  |  |  | 98  | 96  | 94  |  |  | 91  |
| 3   | 106 | 100 | 96  | 93  |  | 104 | 99  | 95  | 92  |  | 96  | 93  | 91  |  |  | 94  | 92  | 89  |  |  | 87  |
| 4   | 102 | 95  | 91  | 87  |  | 100 | 94  | 90  | 87  |  | 92  | 89  | 86  |  |  | 90  | 87  | 85  |  |  | 83  |
| 5   | 98  | 91  | 86  | 83  |  | 96  | 90  | 85  | 82  |  | 88  | 84  | 81  |  |  | 87  | 83  | 81  |  |  | 79  |
| 6   | 94  | 87  | 82  | 78  |  | 93  | 86  | 81  | 78  |  | 85  | 81  | 78  |  |  | 83  | 80  | 77  |  |  | 75  |
| 7   | 91  | 83  | 78  | 75  |  | 89  | 82  | 78  | 74  |  | 81  | 77  | 74  |  |  | 80  | 76  | 74  |  |  | 72  |
| 8   | 87  | 80  | 75  | 71  |  | 86  | 79  | 74  | 71  |  | 78  | 74  | 71  |  |  | 77  | 73  | 71  |  |  | 69  |
| 9   | 84  | 76  | 72  | 68  |  | 83  | 76  | 71  | 68  |  | 75  | 71  | 68  |  |  | 74  | 70  | 68  |  |  | 66  |
| 10  | 81  | 73  | 69  | 65  |  | 80  | 73  | 68  | 65  |  | 72  | 68  | 65  |  |  | 72  | 68  | 65  |  |  | 64  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1672444 |
| 5°  | 1638628 |
| 10° | 1456037 |
| 15° | 1142357 |
| 20° | 768309  |
| 25° | 447006  |
| 30° | 223903  |
| 35° | 104455  |
| 40° | 48744   |
| 45° | 20597   |
| 50° | 9943    |
| 55° | 6348    |
| 60° | 3641    |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P224588

CATALOG NUMBER: LSSQWM2B20FL408050D010 2LBDL\*GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 385.8  | 20.9      |
| 10°-20°   | 773.3  | 41.9      |
| 20°-30°   | 488.9  | 26.5      |
| 30°-40°   | 152.1  | 8.3       |
| 40°-50°   | 33.8   | 1.8       |
| 50°-60°   | 8.6    | 0.5       |
| 60°-70°   | 1.1    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1647.9 | 89.4      |
| 0°-40°    | 1800.0 | 97.6      |
| 0°-60°    | 1842.5 | 99.9      |
| 0°-90°    | 1843.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1843.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4318 |      |
| 5°  | 4214 | 386  |
| 15° | 2849 | 773  |
| 25° | 1046 | 489  |
| 35° | 221  | 152  |
| 45° | 38   | 34   |
| 55° | 9    | 9    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P224588

CATALOG NUMBER: LSSQWM2B20FL408050D010 2LBDL\*GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4317.7 |
| 2.5°  | 4298.9 |
| 5°    | 4214.3 |
| 7.5°  | 4014.5 |
| 10°   | 3701.9 |
| 12.5° | 3307.0 |
| 15°   | 2848.7 |
| 17.5° | 2352.8 |
| 20°   | 1863.9 |
| 22.5° | 1424.3 |
| 25°   | 1045.9 |
| 27.5° | 733.3  |
| 30°   | 500.6  |
| 32.5° | 331.4  |
| 35°   | 220.9  |
| 37.5° | 148.1  |
| 40°   | 96.4   |
| 42.5° | 58.8   |
| 45°   | 37.6   |
| 47.5° | 25.9   |
| 50°   | 16.5   |
| 52.5° | 11.8   |
| 55°   | 9.4    |
| 57.5° | 7.1    |
| 60°   | 4.7    |
| 62.5° | 2.4    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)