

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224450

Luminaire Tested: **LD2B10D010 EU2B10FL409027 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409027 2LBDL*WH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 759.9 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224450

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224450

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			75
7	90	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	701135
5°	674612
10°	593797
15°	466415
20°	317109
25°	185188
30°	94329
35°	44638
40°	19467
45°	8436
50°	4037
55°	2634
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224450

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	20.9
10°-20°	316.3	41.6
20°-30°	203.0	26.7
30°-40°	64.4	8.5
40°-50°	13.8	1.8
50°-60°	3.5	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.8	89.2
0°-40°	742.2	97.7
0°-60°	759.5	99.9
0°-90°	759.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1810	
5°	1735	158
15°	1163	316
25°	433	203
35°	94	64
45°	15	14
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224450

CATALOG NUMBER: LD2B10D010 EU2B10FL409027 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1810.1
2.5°	1792.7
5°	1735.0
7.5°	1640.6
10°	1509.7
12.5°	1349.9
15°	1163.1
17.5°	963.8
20°	769.3
22.5°	587.3
25°	433.3
27.5°	309.1
30°	210.9
32.5°	141.5
35°	94.4
37.5°	62.6
40°	38.5
42.5°	24.1
45°	15.4
47.5°	10.6
50°	6.7
52.5°	4.8
55°	3.9
57.5°	2.9
60°	1.9
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)