

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223945

Luminaire Tested: **LD2B10D010 EU2B10SP159027 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10SP159027 2LBDL*GPH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 420.3 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223945

CATALOG NUMBER: LD2B10D010 EU2B10SP159027 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P223945

CATALOG NUMBER: LD2B10D010 EU2B10SP159027 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																											
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98									98																											
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96									96																											
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94									94																											
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	91									91																											
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	89									89																											
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	88									88																											
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	86									86																											
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	85									85																											
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	84									84																											
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	83									83																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2019622
5°	1460001
10°	425062
15°	149136
20°	63851
25°	28721
30°	11092
35°	5532
40°	3691
45°	2410
50°	1326
55°	1013
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223945

CATALOG NUMBER: LD2B10D010 EU2B10SP159027 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.7	63.2
10°-20°	108.1	25.7
20°-30°	33.2	7.9
30°-40°	8.2	1.9
40°-50°	3.4	0.8
50°-60°	1.5	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	407.0	96.8
0°-40°	415.2	98.8
0°-60°	420.0	99.9
0°-90°	420.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5214	
5°	3755	266
15°	372	108
25°	67	33
35°	12	8
45°	4	3
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223945

CATALOG NUMBER: LD2B10D010 EU2B10SP159027 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5214.0
1°	5134.4
2°	4940.0
3°	4630.2
4°	4225.4
5°	3754.9
6°	3224.4
7°	2648.7
8°	2064.9
9°	1519.0
10°	1080.7
11°	774.5
12°	582.3
13°	474.2
14°	415.0
15°	371.9
17.5°	229.4
20°	154.9
22.5°	103.8
25°	67.2
27.5°	40.9
30°	24.8
32.5°	16.1
35°	11.7
37.5°	9.5
40°	7.3
42.5°	5.8
45°	4.4
47.5°	2.9
50°	2.2
52.5°	2.2
55°	1.5
57.5°	1.5
60°	0.7
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223945

CATALOG NUMBER: LD2B10D010 EU2B10SP159027 2LBDL*GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)