

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224698

Luminaire Tested: **LD2B10D010 EU2B10FL409727 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409727 2LBD*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 709.8 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224698

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224698

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86				86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79				79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75				75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72				72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66				66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	642607
5°	630870
10°	560837
15°	441071
20°	293490
25°	168519
30°	85115
35°	40051
40°	16130
45°	7998
50°	4399
55°	3106
60°	2789
65°	1650
70°	2039
75°	1347
80°	2008
85°	0



TEST NUMBER: P224698

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	20.9
10°-20°	297.9	42.0
20°-30°	185.4	26.1
30°-40°	57.0	8.0
40°-50°	12.5	1.8
50°-60°	4.5	0.6
60°-70°	2.2	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.9	89.0
0°-40°	688.9	97.1
0°-60°	705.9	99.5
0°-90°	709.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1659	
5°	1622	149
15°	1100	298
25°	394	185
35°	85	57
45°	15	13
55°	5	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224698

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1659.0
2.5°	1651.7
5°	1622.5
7.5°	1548.8
10°	1425.9
12.5°	1278.4
15°	1099.9
17.5°	905.1
20°	712.0
22.5°	539.9
25°	394.3
27.5°	277.7
30°	190.3
32.5°	128.4
35°	84.7
37.5°	51.0
40°	31.9
42.5°	21.9
45°	14.6
47.5°	10.0
50°	7.3
52.5°	6.4
55°	4.6
57.5°	3.6
60°	3.6
62.5°	2.7
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)