

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224748

Luminaire Tested: **LSSQWM2B20FL409050D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409050D010 2LBD*MW
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1628.1 lumens
Efficiency: N/A
Efficacy: 77.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224748

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224748

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	86	82	78	93	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1473851
5°	1447014
10°	1286318
15°	1011628
20°	673172
25°	386488
30°	195233
35°	91830
40°	36963
45°	18296
50°	10063
55°	7023
60°	6507
65°	3849
70°	4757
75°	3143
80°	4684
85°	0



TEST NUMBER: P224748

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.8	20.9
10°-20°	683.4	42.0
20°-30°	425.1	26.1
30°-40°	130.7	8.0
40°-50°	28.7	1.8
50°-60°	10.2	0.6
60°-70°	5.2	0.3
70°-80°	3.0	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1449.3	89.0
0°-40°	1580.0	97.1
0°-60°	1619.0	99.4
0°-90°	1628.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1628.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3805	
5°	3722	341
15°	2523	683
25°	904	425
35°	194	131
45°	33	29
55°	10	10
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224748

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3805.0
2.5°	3788.3
5°	3721.5
7.5°	3552.3
10°	3270.4
12.5°	2932.1
15°	2522.7
17.5°	2075.8
20°	1633.1
22.5°	1238.4
25°	904.3
27.5°	636.9
30°	436.5
32.5°	294.5
35°	194.2
37.5°	116.9
40°	73.1
42.5°	50.1
45°	33.4
47.5°	23.0
50°	16.7
52.5°	14.6
55°	10.4
57.5°	8.4
60°	8.4
62.5°	6.3
65°	4.2
67.5°	4.2
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)