

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224973

Luminaire Tested: **LD2B10D010 EU2B10FL409727 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409727 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 672.4 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224973

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224973

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76	76	76	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73	73	73	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70	70	70	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67	67	67	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65	65	65	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	645009
5°	619827
10°	539558
15°	421341
20°	280217
25°	160442
30°	79748
35°	36647
40°	14714
45°	6738
50°	3134
55°	1756
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224973

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	21.6
10°-20°	284.9	42.4
20°-30°	176.3	26.2
30°-40°	52.8	7.8
40°-50°	10.6	1.6
50°-60°	2.6	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.3	90.2
0°-40°	659.1	98.0
0°-60°	672.3	100.0
0°-90°	672.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	672.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1665	
5°	1594	145
15°	1051	285
25°	375	176
35°	78	53
45°	12	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224973

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1665.2
1°	1656.1
2°	1647.7
3°	1630.9
4°	1615.4
5°	1594.1
6°	1565.0
7°	1528.2
8°	1481.0
9°	1427.4
10°	1371.8
11°	1314.3
12°	1252.9
13°	1189.0
14°	1120.5
15°	1050.7
17.5°	866.5
20°	679.8
22.5°	514.4
25°	375.4
27.5°	263.6
30°	178.3
32.5°	117.6
35°	77.5
37.5°	48.5
40°	29.1
42.5°	18.7
45°	12.3
47.5°	7.8
50°	5.2
52.5°	3.9
55°	2.6
57.5°	1.9
60°	1.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224973

CATALOG NUMBER: LD2B10D010 EU2B10FL409727 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)