

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225414

Luminaire Tested: **LSSQWM2B20FL409050D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B20FL409050D010 2LBDC*MB
Description: 2000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1620.7 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225414

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225414

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	103	100		108	104	101	99		101	99	96		98	96	94		96	94	92
3	106	100	96	93		104	99	95	92		97	93	91		94	92	89		92	90	88
4	102	95	91	87		100	94	90	87		92	89	86		90	87	85		89	86	84
5	98	91	86	83		96	90	86	82		88	85	82		87	84	81		85	83	80
6	94	87	82	79		93	86	82	78		85	81	78		84	80	77		82	79	77
7	91	83	78	75		90	83	78	75		81	77	74		80	77	74		79	76	74
8	87	80	75	72		86	79	75	71		78	74	71		77	74	71		76	73	71
9	84	77	72	69		83	76	72	68		75	71	68		74	71	68		74	70	68
10	82	74	69	66		81	73	69	66		73	68	65		72	68	65		71	68	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1466414
5°	1440910
10°	1285414
15°	1016039
20°	677459
25°	393027
30°	196709
35°	92539
40°	36154
45°	16160
50°	7593
55°	4254
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225414

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.7	21.0
10°-20°	685.8	42.3
20°-30°	431.4	26.6
30°-40°	131.9	8.1
40°-50°	25.9	1.6
50°-60°	5.8	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1456.9	89.9
0°-40°	1588.7	98.0
0°-60°	1620.4	100.0
0°-90°	1620.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1620.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3786	
5°	3706	340
15°	2534	686
25°	920	431
35°	196	132
45°	30	26
55°	6	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225414

CATALOG NUMBER: LSSQWM2B20FL409050D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3785.8
2.5°	3777.3
5°	3705.8
7.5°	3537.4
10°	3268.1
12.5°	2931.4
15°	2533.7
17.5°	2091.7
20°	1643.5
22.5°	1260.5
25°	919.6
27.5°	648.1
30°	439.8
32.5°	296.7
35°	195.7
37.5°	119.9
40°	71.5
42.5°	46.3
45°	29.5
47.5°	18.9
50°	12.6
52.5°	8.4
55°	6.3
57.5°	4.2
60°	2.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)