

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225432

Luminaire Tested: **LSR2B05FL408027D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL408027D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 689.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225432

CATALOG NUMBER: LSR2B05FL408027D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225432

CATALOG NUMBER: LSR2B05FL408027D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86	86	86	86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81	81	81	81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77	77	77	77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74	74	74	74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70	70	70	70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67	67	67	67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64	64	64	64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62	62	62	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	599147
5°	577678
10°	508053
15°	398203
20°	275806
25°	169930
30°	94553
35°	50454
40°	25029
45°	12764
50°	6990
55°	4592
60°	2247
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225432

CATALOG NUMBER: LSR2B05FL408027D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.5	19.7
10°-20°	271.2	39.4
20°-30°	185.3	26.9
30°-40°	70.6	10.3
40°-50°	19.6	2.8
50°-60°	6.1	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.0	85.9
0°-40°	662.7	96.2
0°-60°	688.4	99.9
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1547	
5°	1486	136
15°	993	271
25°	398	185
35°	107	71
45°	23	20
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225432

CATALOG NUMBER: LSR2B05FL408027D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1546.8
2.5°	1530.3
5°	1485.7
7.5°	1402.3
10°	1291.7
12.5°	1151.1
15°	993.0
17.5°	831.1
20°	669.1
22.5°	525.6
25°	397.6
27.5°	291.9
30°	211.4
32.5°	150.3
35°	106.7
37.5°	74.7
40°	49.5
42.5°	33.0
45°	23.3
47.5°	16.5
50°	11.6
52.5°	8.7
55°	6.8
57.5°	4.8
60°	2.9
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)