

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B05FL409727D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05FL409727D010 2LBD*LI
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 537.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B05FL409727D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B05FL409727D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	515131
5°	495014
10°	430923
15°	336488
20°	223786
25°	128131
30°	63691
35°	29270
40°	11731
45°	5368
50°	2471
55°	1418
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05FL409727D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.9	21.6
10°-20°	227.5	42.4
20°-30°	140.8	26.2
30°-40°	42.1	7.8
40°-50°	8.4	1.6
50°-60°	2.0	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.2	90.2
0°-40°	526.4	98.0
0°-60°	536.9	100.0
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1330	
5°	1273	116
15°	839	228
25°	300	141
35°	62	42
45°	10	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05FL409727D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1329.9
1°	1322.7
2°	1315.9
3°	1302.5
4°	1290.1
5°	1273.1
6°	1249.9
7°	1220.5
8°	1182.8
9°	1140.0
10°	1095.6
11°	1049.7
12°	1000.6
13°	949.5
14°	894.8
15°	839.1
17.5°	692.0
20°	542.9
22.5°	410.8
25°	299.8
27.5°	210.6
30°	142.4
32.5°	93.9
35°	61.9
37.5°	38.7
40°	23.2
42.5°	15.0
45°	9.8
47.5°	6.2
50°	4.1
52.5°	3.1
55°	2.1
57.5°	1.5
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#
CATALOG NUMBER: LSR2B05FL409727D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)