

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224479

Luminaire Tested: **LSSQ2B05FL408030D010 2LBDL\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224479  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B05FL408030D010 2LBDL\*WH  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 737.6 lumens  
Efficiency: N/A  
Efficacy: 101.0 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224479

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDL\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P224479

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDL\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87				87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79				79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75				75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72				72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66				66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	680528
5°	654782
10°	576334
15°	452700
20°	307793
25°	179717
30°	91556
35°	43314
40°	18911
45°	8217
50°	3917
55°	2499
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224479

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDL\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.8	20.9
10°-20°	307.0	41.6
20°-30°	197.0	26.7
30°-40°	62.5	8.5
40°-50°	13.4	1.8
50°-60°	3.4	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.8	89.2
0°-40°	720.3	97.7
0°-60°	737.1	99.9
0°-90°	737.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1757	
5°	1684	154
15°	1129	307
25°	420	197
35°	92	63
45°	15	13
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224479

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDL\*WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1756.9
2.5°	1740.0
5°	1684.0
7.5°	1592.4
10°	1465.3
12.5°	1310.2
15°	1128.9
17.5°	935.4
20°	746.7
22.5°	570.0
25°	420.5
27.5°	300.0
30°	204.7
32.5°	137.4
35°	91.6
37.5°	60.7
40°	37.4
42.5°	23.4
45°	15.0
47.5°	10.3
50°	6.5
52.5°	4.7
55°	3.7
57.5°	2.8
60°	1.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)