

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225433

Luminaire Tested: **LSSQ2B05FL408030D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05FL408030D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 702.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225433

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225433

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90			90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86			86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81			81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77			77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74			74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70			70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67			67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64			64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62			62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	610419
5°	588565
10°	517650
15°	405742
20°	281041
25°	173135
30°	96342
35°	51400
40°	25484
45°	12983
50°	7171
55°	4660
60°	2324
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225433

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	19.7
10°-20°	276.4	39.4
20°-30°	188.8	26.9
30°-40°	72.0	10.3
40°-50°	20.0	2.8
50°-60°	6.2	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.2	85.9
0°-40°	675.2	96.2
0°-60°	701.4	99.9
0°-90°	702.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	702.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1576	
5°	1514	138
15°	1012	276
25°	405	189
35°	109	72
45°	24	20
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225433

CATALOG NUMBER: LSSQ2B05FL408030D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1575.9
2.5°	1559.1
5°	1513.7
7.5°	1428.7
10°	1316.1
12.5°	1172.8
15°	1011.8
17.5°	846.8
20°	681.8
22.5°	535.5
25°	405.1
27.5°	297.4
30°	215.4
32.5°	153.1
35°	108.7
37.5°	76.1
40°	50.4
42.5°	33.6
45°	23.7
47.5°	16.8
50°	11.9
52.5°	8.9
55°	6.9
57.5°	4.9
60°	3.0
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)