

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264965

Luminaire Tested: **LD2B10D010 EU2B1010SP159030 2LBDL\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264965  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP159030 2LBDL\*LI  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 778.0 lumens  
Efficiency: N/A  
Efficacy: 75.5 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264965

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBDL\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P264965

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBDL\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100													
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97	97	97	97													
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94	94	94	94													
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92	92	92	92													
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89	89	89	89													
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87	87	87	87													
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85	85	85	85													
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83	83	83	83													
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81	81	81	81													
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79	79	79	79													
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78	78	78	78													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2746496
5°	2235393
10°	1207494
15°	481448
20°	193052
25°	92433
30°	47911
35°	25356
40°	14040
45°	8721
50°	5987
55°	4043
60°	3059
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264965

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBDL\*LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	363.0	46.7
10°-20°	286.4	36.8
20°-30°	84.5	10.9
30°-40°	28.1	3.6
40°-50°	10.6	1.4
50°-60°	4.7	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.9	94.3
0°-40°	762.0	97.9
0°-60°	777.3	99.9
0°-90°	778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5567	
5°	4514	363
15°	943	286
25°	170	84
35°	42	28
45°	12	11
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264965

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBDL\*LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5566.9
2.5°	5342.5
5°	4513.7
7.5°	3477.6
10°	2410.3
12.5°	1542.5
15°	942.6
17.5°	574.9
20°	367.7
22.5°	246.2
25°	169.8
27.5°	120.0
30°	84.1
32.5°	59.2
35°	42.1
37.5°	29.6
40°	21.8
42.5°	17.1
45°	12.5
47.5°	10.9
50°	7.8
52.5°	6.2
55°	4.7
57.5°	4.7
60°	3.1
62.5°	1.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)