

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264299

Luminaire Tested: **LD2B10D010 EU2B1010SP159030 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159030 2LBSQC*MB
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 768.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264299

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264299

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98																			
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96																			
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94																			
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92																			
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90																			
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89																			
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87																			
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86																			
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85																			
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3623890
5°	2904719
10°	1267812
15°	392881
20°	136979
25°	60479
30°	27402
35°	14214
40°	8115
45°	3837
50°	2456
55°	1376
60°	789
65°	934
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264299

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	445.4	58.0
10°-20°	243.9	31.8
20°-30°	55.6	7.2
30°-40°	16.0	2.1
40°-50°	4.9	0.6
50°-60°	1.5	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.9	97.0
0°-40°	760.9	99.1
0°-60°	767.3	99.9
0°-90°	768.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	768.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7345	
5°	5865	445
15°	769	244
25°	111	56
35°	24	16
45°	6	5
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264299

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	7345.3
1°	7253.9
2°	7063.9
3°	6769.2
4°	6364.1
5°	5865.2
6°	5253.6
7°	4570.3
8°	3857.1
9°	3166.7
10°	2530.7
11°	1992.4
12°	1568.4
13°	1234.2
14°	974.9
15°	769.2
16°	606.9
17°	483.1
18°	388.5
19°	316.0
20°	260.9
22.5°	168.7
25°	111.1
26°	93.8
27°	79.6
28°	67.0
29°	56.0
30°	48.1
32.5°	33.1
35°	23.6
37.5°	17.3
40°	12.6
42.5°	8.7
45°	5.5
47.5°	3.9
50°	3.2
52.5°	2.4
55°	1.6
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8



TEST NUMBER: P264299

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)