

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225337

Luminaire Tested: **LSSQWM2B05FL408030D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408030D010 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 670.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225337

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225337

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	606545
5°	595525
10°	529371
15°	416329
20°	277043
25°	159031
30°	80329
35°	37782
40°	15220
45°	7560
50°	4158
55°	2904
60°	2634
65°	1558
70°	1925
75°	1347
80°	2008
85°	0



TEST NUMBER: P225337

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.3	20.9
10°-20°	281.2	42.0
20°-30°	175.0	26.1
30°-40°	53.8	8.0
40°-50°	11.8	1.8
50°-60°	4.2	0.6
60°-70°	2.1	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.5	89.0
0°-40°	650.2	97.0
0°-60°	666.3	99.4
0°-90°	670.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	670.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1566	
5°	1532	140
15°	1038	281
25°	372	175
35°	80	54
45°	14	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225337

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1565.9
2.5°	1559.1
5°	1531.6
7.5°	1461.9
10°	1345.9
12.5°	1206.7
15°	1038.2
17.5°	854.3
20°	672.1
22.5°	509.7
25°	372.1
27.5°	262.1
30°	179.6
32.5°	121.2
35°	79.9
37.5°	48.1
40°	30.1
42.5°	20.6
45°	13.8
47.5°	9.5
50°	6.9
52.5°	6.0
55°	4.3
57.5°	3.4
60°	3.4
62.5°	2.6
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)