

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224795

Luminaire Tested: **LSSQWM2B05FL408030D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL408030D010 2LBDL*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 717.9 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224795

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224795

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	650005
5°	638179
10°	567287
15°	446164
20°	296870
25°	170443
30°	86099
35°	40524
40°	16282
45°	8053
50°	4459
55°	3106
60°	2866
65°	1650
70°	2039
75°	1347
80°	2008
85°	0



TEST NUMBER: P224795

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	20.9
10°-20°	301.4	42.0
20°-30°	187.5	26.1
30°-40°	57.7	8.0
40°-50°	12.7	1.8
50°-60°	4.5	0.6
60°-70°	2.3	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.2	89.0
0°-40°	696.8	97.1
0°-60°	714.0	99.5
0°-90°	717.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1678	
5°	1641	150
15°	1113	301
25°	399	187
35°	86	58
45°	15	13
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224795

CATALOG NUMBER: LSSQWM2B05FL408030D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1678.1
2.5°	1670.8
5°	1641.3
7.5°	1566.7
10°	1442.3
12.5°	1293.1
15°	1112.6
17.5°	915.5
20°	720.2
22.5°	546.2
25°	398.8
27.5°	280.9
30°	192.5
32.5°	129.9
35°	85.7
37.5°	51.6
40°	32.2
42.5°	22.1
45°	14.7
47.5°	10.1
50°	7.4
52.5°	6.4
55°	4.6
57.5°	3.7
60°	3.7
62.5°	2.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)