

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222815

Luminaire Tested: **LSSQ2B05NFL259030D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05NFL259030D010 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222815

CATALOG NUMBER: LSSQ2B05NFL259030D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P222815

CATALOG NUMBER: LSSQ2B05NFL259030D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97			97																
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95			95																
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92			92																
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90			90																
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88			88																
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86			86																
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84			84																
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82			82																
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80			80																
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79			79																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1410946
5°	1302760
10°	881787
15°	299996
20°	110182
25°	58424
30°	30012
35°	13997
40°	4601
45°	2301
50°	1085
55°	405
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222815

CATALOG NUMBER: LSSQ2B05NFL259030D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	285.0	46.4
10°-20°	239.6	39.0
20°-30°	65.8	10.7
30°-40°	19.2	3.1
40°-50°	3.5	0.6
50°-60°	0.8	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.4	96.2
0°-40°	609.6	99.3
0°-60°	613.9	100.0
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3643	
5°	3350	285
15°	748	240
25°	137	66
35°	30	19
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222815

CATALOG NUMBER: LSSQ2B05NFL259030D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3642.6
1°	3621.5
2°	3584.0
3°	3530.1
4°	3456.4
5°	3350.5
6°	3206.0
7°	3025.1
8°	2804.4
9°	2543.7
10°	2241.9
11°	1911.1
12°	1567.0
13°	1238.6
14°	958.6
15°	748.1
17.5°	422.1
20°	267.3
22.5°	190.5
25°	136.7
27.5°	96.8
30°	67.1
32.5°	47.2
35°	29.6
37.5°	12.1
40°	9.1
42.5°	6.7
45°	4.2
47.5°	2.4
50°	1.8
52.5°	1.2
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222815

CATALOG NUMBER: LSSQ2B05NFL259030D010 2LBDC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)