

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224871

Luminaire Tested: **LD2B10D010 EU2B10FL409730 2LBD\*B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224871  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL409730 2LBD\*B  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
SPUN ROUND TRIM WITH BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 745.8 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224871

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBD\*B

### Luminous Intensity Polar Plot





TEST NUMBER: P224871

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBD\*B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79			79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72			72
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69			69
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67			67
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	674795
5°	663064
10°	591516
15°	467538
20°	311751
25°	180871
30°	90527
35°	42605
40°	16636
45°	7450
50°	3495
55°	1958
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224871

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBD\*B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.3	21.0
10°-20°	315.6	42.3
20°-30°	198.5	26.6
30°-40°	60.7	8.1
40°-50°	11.9	1.6
50°-60°	2.7	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.4	89.9
0°-40°	731.1	98.0
0°-60°	745.7	100.0
0°-90°	745.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	745.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1742	
5°	1705	156
15°	1166	316
25°	423	199
35°	90	61
45°	14	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224871

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBD\*B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1742.1
2.5°	1738.2
5°	1705.3
7.5°	1627.8
10°	1503.9
12.5°	1348.9
15°	1165.9
17.5°	962.6
20°	756.3
22.5°	580.1
25°	423.2
27.5°	298.3
30°	202.4
32.5°	136.5
35°	90.1
37.5°	55.2
40°	32.9
42.5°	21.3
45°	13.6
47.5°	8.7
50°	5.8
52.5°	3.9
55°	2.9
57.5°	1.9
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)