

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B05WFL559730D010 2LBDL\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B05WFL559730D010 2LBDL\*GPH  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 485.0 lumens  
Efficiency: N/A  
Efficacy: 66.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LSR2B05WFL559730D010 2LBDL\*GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL559730D010 2LBDL\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																											
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74																											
5	92	83	77	73	90	82	77	72	80	75	72	79	74	71	77	73	70	69																											
6	87	78	72	67	85	77	71	67	75	70	67	74	70	66	73	69	66	64																											
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60																											
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																											
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																											
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	231091
5°	228552
10°	211253
15°	184986
20°	159482
25°	136166
30°	107702
35°	74523
40°	48238
45°	29252
50°	17114
55°	9590
60°	3641
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL559730D010 2LBDL\*GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.5	11.2
10°-20°	128.6	26.5
20°-30°	144.7	29.8
30°-40°	99.8	20.6
40°-50°	43.1	8.9
50°-60°	13.4	2.8
60°-70°	0.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.8	67.6
0°-40°	427.6	88.2
0°-60°	484.1	99.8
0°-90°	485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	485.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	597	
5°	588	54
15°	461	129
25°	319	145
35°	158	100
45°	53	43
55°	14	13
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL559730D010 2LBDL\*GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	596.6
2.5°	595.2
5°	587.8
7.5°	568.2
10°	537.1
12.5°	500.5
15°	461.3
17.5°	422.1
20°	386.9
22.5°	353.1
25°	318.6
27.5°	282.1
30°	240.8
32.5°	197.5
35°	157.6
37.5°	123.8
40°	95.4
42.5°	71.7
45°	53.4
47.5°	39.2
50°	28.4
52.5°	20.3
55°	14.2
57.5°	9.5
60°	4.7
62.5°	1.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)