

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224246

Luminaire Tested: **LD2B10D010 EU2B10FL409730 2LBDSQLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224246  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL409730 2LBDSQLC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SQUARE CAST TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 669.8 lumens  
Efficiency: N/A  
Efficacy: 65.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224246

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDSQLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P224246

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDSQLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83	83	83	83
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76	76	76	76
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72	72	72	72
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69	69	69	69
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	67	67
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	609683
5°	597975
10°	531181
15°	419176
20°	279599
25°	160912
30°	81492
35°	38207
40°	15624
45°	7066
50°	3616
55°	2296
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224246

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDSQLC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.8	21.0
10°-20°	282.5	42.2
20°-30°	176.9	26.4
30°-40°	54.7	8.2
40°-50°	11.3	1.7
50°-60°	3.1	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.2	89.6
0°-40°	654.9	97.8
0°-60°	669.4	99.9
0°-90°	669.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1574	
5°	1538	141
15°	1045	282
25°	376	177
35°	81	55
45°	13	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224246

CATALOG NUMBER: LD2B10D010 EU2B10FL409730 2LBDSQLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1574.0
2.5°	1566.3
5°	1537.9
7.5°	1465.7
10°	1350.5
12.5°	1208.7
15°	1045.3
17.5°	857.1
20°	678.3
22.5°	515.8
25°	376.5
27.5°	264.8
30°	182.2
32.5°	122.1
35°	80.8
37.5°	50.7
40°	30.9
42.5°	19.8
45°	12.9
47.5°	8.6
50°	6.0
52.5°	4.3
55°	3.4
57.5°	2.6
60°	1.7
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)