

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223569

Luminaire Tested: **LSSQ2B05SP159730D010 2LBDLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B05SP159730D010 2LBDLC\*MB  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
SPOT OPTIC  
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 299.0 lumens  
Efficiency: N/A  
Efficacy: 41.0 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223569

CATALOG NUMBER: LSSQ2B05SP159730D010 2LBDLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P223569

CATALOG NUMBER: LSSQ2B05SP159730D010 2LBDLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																											
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																											
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94																											
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																											
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91																											
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90																											
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88																											
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87																											
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86																											
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1436744
5°	1038631
10°	302386
15°	106107
20°	45425
25°	20429
30°	7917
35°	3925
40°	2629
45°	1698
50°	964
55°	675
60°	387
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223569

CATALOG NUMBER: LSSQ2B05SP159730D010 2LBDLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.0	63.2
10°-20°	76.9	25.7
20°-30°	23.6	7.9
30°-40°	5.8	1.9
40°-50°	2.4	0.8
50°-60°	1.0	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.5	96.8
0°-40°	295.3	98.8
0°-60°	298.8	99.9
0°-90°	299.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	299.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3709	
5°	2671	189
15°	265	77
25°	48	24
35°	8	6
45°	3	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223569

CATALOG NUMBER: LSSQ2B05SP159730D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3709.2
1°	3652.6
2°	3514.3
3°	3293.9
4°	3006.0
5°	2671.2
6°	2293.8
7°	1884.2
8°	1468.9
9°	1080.6
10°	768.8
11°	551.0
12°	414.3
13°	337.3
14°	295.2
15°	264.6
17.5°	163.2
20°	110.2
22.5°	73.8
25°	47.8
27.5°	29.1
30°	17.7
32.5°	11.4
35°	8.3
37.5°	6.8
40°	5.2
42.5°	4.2
45°	3.1
47.5°	2.1
50°	1.6
52.5°	1.6
55°	1.0
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223569

CATALOG NUMBER: LSSQ2B05SP159730D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)