

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B05WFL559730D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14809)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B05WFL559730D010 2LBDLC*MB
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 474.0 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559730D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559730D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																											
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																											
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																											
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																											
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																											
7	83	73	67	63	81	73	67	63	71	66	63	70	66	62	69	65	62	60																											
8	79	69	63	59	78	69	63	59	67	62	59	66	62	58	65	61	58	57																											
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53																											
10	71	62	56	52	70	61	56	52	60	55	52	60	55	52	59	55	51	50																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225668
5°	224197
10°	208814
15°	183101
20°	158163
25°	134542
30°	106718
35°	73625
40°	46266
45°	27609
50°	15969
55°	8036
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559730D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	11.3
10°-20°	127.3	26.8
20°-30°	143.3	30.2
30°-40°	98.4	20.8
40°-50°	40.9	8.6
50°-60°	10.6	2.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.1	68.4
0°-40°	422.5	89.1
0°-60°	474.0	100.0
0°-90°	474.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	583	
5°	577	54
15°	457	127
25°	315	143
35°	156	98
45°	50	41
55°	12	11
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B05WFL559730D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	582.6
2.5°	581.9
5°	576.6
7.5°	559.4
10°	530.9
12.5°	495.1
15°	456.6
17.5°	417.5
20°	383.7
22.5°	350.6
25°	314.8
27.5°	278.4
30°	238.6
32.5°	196.2
35°	155.7
37.5°	121.3
40°	91.5
42.5°	68.9
45°	50.4
47.5°	36.5
50°	26.5
52.5°	18.6
55°	11.9
57.5°	4.0
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)