

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225066

Luminaire Tested: **LSSQWM2B05FL409730D010 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14829)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B05FL409730D010 2LBD*WH
Description: 500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 578.0 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225066

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P225066

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			75
7	90	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	533298
5°	513133
10°	451651
15°	354774
20°	241181
25°	140867
30°	71742
35°	33952
40°	14815
45°	6409
50°	3073
55°	1958
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225066

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.5	20.9
10°-20°	240.6	41.6
20°-30°	154.4	26.7
30°-40°	49.0	8.5
40°-50°	10.5	1.8
50°-60°	2.7	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.5	89.2
0°-40°	564.5	97.7
0°-60°	577.7	99.9
0°-90°	578.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	578.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1377	
5°	1320	121
15°	885	241
25°	330	154
35°	72	49
45°	12	10
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225066

CATALOG NUMBER: LSSQWM2B05FL409730D010 2LBD*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1376.8
2.5°	1363.6
5°	1319.7
7.5°	1247.9
10°	1148.3
12.5°	1026.7
15°	884.7
17.5°	733.1
20°	585.1
22.5°	446.7
25°	329.6
27.5°	235.1
30°	160.4
32.5°	107.7
35°	71.8
37.5°	47.6
40°	29.3
42.5°	18.3
45°	11.7
47.5°	8.1
50°	5.1
52.5°	3.7
55°	2.9
57.5°	2.2
60°	1.5
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)