

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224130

Luminaire Tested: **LD2B10D010 EU2B10SP158035 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10SP158035 2LBDSQLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 565.7 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224130

CATALOG NUMBER: LD2B10D010 EU2B10SP158035 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224130

CATALOG NUMBER: LD2B10D010 EU2B10SP158035 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96	96	96	96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94	94	94	94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93	93	93	93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91	91	91	91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90	90	90	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88	88	88	88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	89	88	87	87	87	87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86	86	86	86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85	85	85	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2718317
5°	1965086
10°	572086
15°	200746
20°	85945
25°	38679
30°	14939
35°	7424
40°	4955
45°	3232
50°	1808
55°	1351
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224130

CATALOG NUMBER: LD2B10D010 EU2B10SP158035 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.6	63.2
10°-20°	145.5	25.7
20°-30°	44.7	7.9
30°-40°	11.0	1.9
40°-50°	4.6	0.8
50°-60°	2.0	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.8	96.8
0°-40°	558.8	98.8
0°-60°	565.4	99.9
0°-90°	565.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	565.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7018	
5°	5054	358
15°	501	145
25°	90	45
35°	16	11
45°	6	5
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224130

CATALOG NUMBER: LD2B10D010 EU2B10SP158035 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7017.8
1°	6910.6
2°	6649.0
3°	6232.0
4°	5687.2
5°	5053.9
6°	4339.9
7°	3564.9
8°	2779.2
9°	2044.6
10°	1454.5
11°	1042.4
12°	783.8
13°	638.2
14°	558.6
15°	500.6
17.5°	308.8
20°	208.5
22.5°	139.6
25°	90.5
27.5°	55.1
30°	33.4
32.5°	21.6
35°	15.7
37.5°	12.8
40°	9.8
42.5°	7.9
45°	5.9
47.5°	3.9
50°	3.0
52.5°	3.0
55°	2.0
57.5°	2.0
60°	1.0
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224130

CATALOG NUMBER: LD2B10D010 EU2B10SP158035 2LBDSQLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)