

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B1010SP159027 2LBPIN**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14823)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP159027 2LBPIN  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
SPOT OPTIC  
ROUND PINHOLE BLACK OCULUS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 373.4 lumens  
Efficiency: N/A  
Efficacy: 36.2 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBPIN

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBPIN

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96	96	96	96
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	95	95	95	95
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93	93	93	93
5	105	101	97	95	104	100	97	95	98	96	94	97	95	93	96	94	92	91	91	91	91
6	103	98	95	93	102	98	95	92	97	94	92	95	93	91	94	92	91	90	90	90	90
7	101	96	93	91	101	96	93	91	95	92	90	94	92	90	93	91	89	89	89	89	89
8	100	95	91	89	99	94	91	89	93	91	89	93	90	88	92	90	88	87	87	87	87
9	98	93	90	88	97	93	90	88	92	89	87	91	89	87	91	89	87	86	86	86	86
10	97	92	88	86	96	91	88	86	91	88	86	90	88	86	90	87	86	85	85	85	85

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1713073
5°	1270011
10°	394879
15°	125802
20°	54843
25°	24327
30°	8993
35°	4352
40°	2984
45°	1808
50°	1025
55°	1148
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBPIN

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	236.2	63.3
10°-20°	98.7	26.4
20°-30°	28.2	7.6
30°-40°	6.3	1.7
40°-50°	2.6	0.7
50°-60°	1.2	0.3
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.1	97.2
0°-40°	369.4	98.9
0°-60°	373.3	100.0
0°-90°	373.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	373.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4421	
5°	3265	236
15°	314	99
25°	57	28
35°	9	6
45°	3	3
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010SP159027 2LBPIN

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4421.0
2.5°	4145.0
5°	3265.1
7.5°	2081.7
10°	1003.6
12.5°	466.7
15°	313.6
17.5°	194.9
20°	133.0
22.5°	90.3
25°	56.9
27.5°	33.5
30°	20.1
32.5°	12.5
35°	9.2
37.5°	6.7
40°	5.9
42.5°	4.2
45°	3.3
47.5°	2.5
50°	1.7
52.5°	1.7
55°	1.7
57.5°	0.8
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)