

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265021

Luminaire Tested: **LD2B10D010 EU2B1010SP159035 2LBDL\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P265021  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP159035 2LBDL\*WH  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 833.0 lumens  
Efficiency: N/A  
Efficacy: 80.9 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P265021

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P265021

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |    |    |    |    | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |    |    |    |    |    |    |    | 10 |    |   |  |  |  |  |  |  | 0  |  |  |  |  |  |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 99  | 99  | 97  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 2   | 112 | 108 | 106 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 94  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 3   | 109 | 104 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 96  | 98  | 96  | 94  | 96  | 94  | 93  | 92  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 4   | 105 | 100 | 97  | 94  | 104 | 99  | 96  | 93  | 97  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 89  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 5   | 103 | 97  | 93  | 91  | 101 | 96  | 93  | 90  | 95  | 92  | 89  | 93  | 91  | 89  | 92  | 90  | 88  | 87  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 6   | 100 | 94  | 90  | 88  | 99  | 94  | 90  | 87  | 92  | 89  | 87  | 91  | 88  | 86  | 90  | 88  | 86  | 85  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 7   | 98  | 92  | 88  | 85  | 97  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 88  | 86  | 84  | 83  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 8   | 95  | 89  | 86  | 83  | 94  | 89  | 85  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 81  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 9   | 93  | 87  | 83  | 81  | 92  | 87  | 83  | 81  | 86  | 83  | 81  | 85  | 82  | 80  | 85  | 82  | 80  | 79  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 10  | 91  | 85  | 82  | 79  | 91  | 85  | 81  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 83  | 80  | 78  | 78  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2940683 |
| 5°  | 2393427 |
| 10° | 1292860 |
| 15° | 515516  |
| 20° | 206702  |
| 25° | 98965   |
| 30° | 51329   |
| 35° | 27103   |
| 40° | 15070   |
| 45° | 9280    |
| 50° | 6371    |
| 55° | 4301    |
| 60° | 3256    |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P265021

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL\*WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 388.7  | 46.7      |
| 10°-20°   | 306.6  | 36.8      |
| 20°-30°   | 90.5   | 10.9      |
| 30°-40°   | 30.1   | 3.6       |
| 40°-50°   | 11.3   | 1.4       |
| 50°-60°   | 5.0    | 0.6       |
| 60°-70°   | 0.8    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 785.8  | 94.3      |
| 0°-40°    | 815.9  | 97.9      |
| 0°-60°    | 832.2  | 99.9      |
| 0°-90°    | 833.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 833.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5960 |      |
| 5°  | 4833 | 389  |
| 15° | 1009 | 307  |
| 25° | 182  | 90   |
| 35° | 45   | 30   |
| 45° | 13   | 11   |
| 55° | 5    | 5    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P265021

CATALOG NUMBER: LD2B10D010 EU2B1010SP159035 2LBDL\*WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 5960.5 |
| 2.5°  | 5720.2 |
| 5°    | 4832.8 |
| 7.5°  | 3723.4 |
| 10°   | 2580.7 |
| 12.5° | 1651.5 |
| 15°   | 1009.3 |
| 17.5° | 615.6  |
| 20°   | 393.7  |
| 22.5° | 263.6  |
| 25°   | 181.8  |
| 27.5° | 128.5  |
| 30°   | 90.1   |
| 32.5° | 63.4   |
| 35°   | 45.0   |
| 37.5° | 31.7   |
| 40°   | 23.4   |
| 42.5° | 18.4   |
| 45°   | 13.3   |
| 47.5° | 11.7   |
| 50°   | 8.3    |
| 52.5° | 6.7    |
| 55°   | 5.0    |
| 57.5° | 5.0    |
| 60°   | 3.3    |
| 62.5° | 1.7    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)