

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B1010NFL258040 2LBPIN**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010NFL258040 2LBPIN  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
ROUND PINHOLE BLACK OCULUS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 846.4 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LD2B10D010 EU2B1010NFL258040 2LBPIN

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010NFL258040 2LBPIN

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1987568
5°	1845719
10°	1254478
15°	415034
20°	140984
25°	71400
30°	36868
35°	12110
40°	4502
45°	2466
50°	663
55°	743
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010NFL258040 2LBPIN

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	403.1	47.6
10°-20°	336.8	39.8
20°-30°	81.5	9.6
30°-40°	21.0	2.5
40°-50°	3.5	0.4
50°-60°	0.6	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	821.3	97.0
0°-40°	842.3	99.5
0°-60°	846.4	100.0
0°-90°	846.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5129	
5°	4745	403
15°	1035	337
25°	167	81
35°	26	21
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B1010NFL258040 2LBPIN

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5129.4
2.5°	5043.6
5°	4745.2
7.5°	4127.1
10°	3188.3
12.5°	1972.2
15°	1034.6
17.5°	559.0
20°	341.9
22.5°	236.1
25°	167.0
27.5°	118.0
30°	82.4
32.5°	57.9
35°	25.6
37.5°	11.1
40°	8.9
42.5°	6.7
45°	4.5
47.5°	2.2
50°	1.1
52.5°	1.1
55°	1.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)