

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223131

Luminaire Tested: **LSR2B05NFL258050D010 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223131  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B05NFL258050D010 2LBDL\*H  
Description: 500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 750.0 lumens  
Efficiency: N/A  
Efficacy: 102.7 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223131

CATALOG NUMBER: LSR2B05NFL258050D010 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P223131

CATALOG NUMBER: LSR2B05NFL258050D010 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97			97																
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95			95																
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92			92																
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90			90																
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88			88																
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86			86																
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84			84																
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82			82																
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80			80																
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79			79																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1723496
5°	1591346
10°	1077111
15°	366443
20°	134585
25°	71374
30°	36676
35°	17118
40°	5613
45°	2849
50°	1326
55°	473
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223131

CATALOG NUMBER: LSR2B05NFL258050D010 2LBDL\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	348.1	46.4
10°-20°	292.7	39.0
20°-30°	80.3	10.7
30°-40°	23.4	3.1
40°-50°	4.3	0.6
50°-60°	1.0	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.2	96.2
0°-40°	744.6	99.3
0°-60°	749.9	100.0
0°-90°	750.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4450	
5°	4093	348
15°	914	293
25°	167	80
35°	36	23
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223131

CATALOG NUMBER: LSR2B05NFL258050D010 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4449.5
1°	4423.6
2°	4377.8
3°	4312.1
4°	4221.9
5°	4092.7
6°	3916.1
7°	3695.2
8°	3425.6
9°	3107.2
10°	2738.5
11°	2334.4
12°	1914.1
13°	1513.0
14°	1170.9
15°	913.8
17.5°	515.6
20°	326.5
22.5°	232.7
25°	167.0
27.5°	118.2
30°	82.0
32.5°	57.6
35°	36.2
37.5°	14.8
40°	11.1
42.5°	8.1
45°	5.2
47.5°	3.0
50°	2.2
52.5°	1.5
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223131

CATALOG NUMBER: LSR2B05NFL258050D010 2LBDL\*H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)