

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264767

Luminaire Tested: **LD2B10D010 EU2B1010SP158040 2LBSQLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264767  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP158040 2LBSQLC\*MB  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 969.0 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264767

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBSQLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P264767

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBSQLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3420773
5°	2784176
10°	1503920
15°	599639
20°	240461
25°	115133
30°	59703
35°	31560
40°	17518
45°	10815
50°	7445
55°	4989
60°	3848
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264767

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBSQLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	452.1	46.7
10°-20°	356.7	36.8
20°-30°	105.2	10.9
30°-40°	35.0	3.6
40°-50°	13.2	1.4
50°-60°	5.8	0.6
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.0	94.3
0°-40°	949.1	97.9
0°-60°	968.1	99.9
0°-90°	969.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6934	
5°	5622	452
15°	1174	357
25°	212	105
35°	52	35
45°	16	13
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264767

CATALOG NUMBER: LD2B10D010 EU2B1010SP158040 2LBSQLC\*MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6933.6
2.5°	6654.1
5°	5621.8
7.5°	4331.3
10°	3002.0
12.5°	1921.1
15°	1174.0
17.5°	716.1
20°	458.0
22.5°	306.6
25°	211.5
27.5°	149.4
30°	104.8
32.5°	73.7
35°	52.4
37.5°	36.9
40°	27.2
42.5°	21.3
45°	15.5
47.5°	13.6
50°	9.7
52.5°	7.8
55°	5.8
57.5°	5.8
60°	3.9
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)