

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B05WFL558050D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29157)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B05WFL558050D010 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 759.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.82
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B05WFL558050D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL558050D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87																											
3	102	96	91	86	100	94	90	86	92	88	84	89	86	83	87	84	82	80																											
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																											
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69																											
6	87	78	72	68	86	77	71	67	76	71	67	74	70	66	73	69	66	64																											
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60																											
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56																											
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																											
10	71	62	56	52	70	61	55	52	60	55	52	59	55	51	59	54	51	50																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	368056
5°	363435
10°	334677
15°	294582
20°	252269
25°	212840
30°	166160
35°	114811
40°	73723
45°	45028
50°	26635
55°	15195
60°	4803
65°	733
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL558050D010 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.6	11.4
10°-20°	204.1	26.9
20°-30°	226.3	29.8
30°-40°	153.6	20.2
40°-50°	66.3	8.7
50°-60°	20.8	2.7
60°-70°	1.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.0	68.1
0°-40°	670.6	88.4
0°-60°	757.7	99.8
0°-90°	759.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	950	
5°	935	87
15°	735	204
25°	498	226
35°	243	154
45°	82	66
55°	22	21
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL558050D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	950.2
1°	947.9
2°	944.8
3°	943.2
4°	940.1
5°	934.7
6°	926.1
7°	913.0
8°	895.1
9°	874.2
10°	850.9
11°	827.6
12°	804.4
13°	781.1
14°	757.8
15°	734.6
17.5°	671.7
20°	612.0
22.5°	555.4
25°	498.0
27.5°	438.3
30°	371.5
32.5°	304.1
35°	242.8
37.5°	190.0
40°	145.8
42.5°	110.1
45°	82.2
47.5°	60.5
50°	44.2
52.5°	31.8
55°	22.5
57.5°	14.7
60°	6.2
62.5°	1.6
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B05WFL558050D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)