

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223224

Luminaire Tested: **LD2B10D010 EU2B10NFL258040 2LBDC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223224  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10NFL258040 2LBDC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1064.6 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223224

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P223224

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	94	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2446671
5°	2259038
10°	1529076
15°	520230
20°	191057
25°	101291
30°	52062
35°	24305
40°	7939
45°	3999
50°	1868
55°	675
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223224

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	494.2	46.4
10°-20°	415.5	39.0
20°-30°	114.0	10.7
30°-40°	33.3	3.1
40°-50°	6.1	0.6
50°-60°	1.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.8	96.2
0°-40°	1057.0	99.3
0°-60°	1064.5	100.0
0°-90°	1064.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1064.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6316	
5°	5810	494
15°	1297	416
25°	237	114
35°	51	33
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223224

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6316.5
1°	6279.8
2°	6214.7
3°	6121.4
4°	5993.5
5°	5809.9
6°	5559.3
7°	5245.7
8°	4862.9
9°	4410.9
10°	3887.6
11°	3314.0
12°	2717.2
13°	2147.8
14°	1662.2
15°	1297.3
17.5°	732.0
20°	463.5
22.5°	330.3
25°	237.0
27.5°	167.8
30°	116.4
32.5°	81.8
35°	51.4
37.5°	21.0
40°	15.7
42.5°	11.5
45°	7.3
47.5°	4.2
50°	3.1
52.5°	2.1
55°	1.0
57.5°	1.0
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223224

CATALOG NUMBER: LD2B10D010 EU2B10NFL258040 2LBDC\*MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)